


488

561



FL1 525/50	FL2 585/30	FL3 617/30	FL4 695/50	FL5 785/60
<ul style="list-style-type: none"> <li>EGFP</li> <li>CFSE</li> <li>FITC</li> <li>AF488</li> <li>SYBR Green</li> <li>EYFP</li> <li>mVenus</li> <li>mCitrine</li> <li>LIVE/DEAD GRN</li> <li>Zombie Green</li> </ul>	<ul style="list-style-type: none"> <li>PE</li> <li>mOrange</li> <li>tdTomato</li> <li>DsRed/mRFP</li> </ul>	<ul style="list-style-type: none"> <li>PE-Texas Red</li> <li>PE-Dazzle594</li> <li>PI</li> <li>LIVE/DEAD Red</li> <li>Zombie Red</li> <li>mCherry</li> <li>AF594</li> <li>mKate</li> </ul>	<ul style="list-style-type: none"> <li>7AAD</li> <li>PE-Cy5</li> <li>PerCP</li> <li>PE-Cy5.5</li> <li>PerCP-Cy5.5</li> <li>PerCP-eFluor710</li> <li>mPlum</li> </ul>	<ul style="list-style-type: none"> <li>PE-Cy7</li> </ul>

FSC

BSC

488/561

405/638

405

638

FL6 450/50	FL7 525/50	FL8 585/30	FL9 617/30	FL10 665/30	FL11 720/60	FL12 785/60
<ul style="list-style-type: none"> <li>BV421</li> <li>AF405</li> <li>Zombie Violet</li> <li>LIVE/DEAD Violet</li> <li>DAPI</li> <li>PacBlue</li> <li>mCFP</li> <li>BFP</li> <li>Sytox Blue</li> <li>Hoechst 33342</li> </ul>	<ul style="list-style-type: none"> <li>AmCyan</li> <li>BV510</li> <li>T-Sapphire</li> <li>PacOrange</li> <li>Zombie Aqua</li> <li>LIVE/DEAD Aqua</li> </ul>	<ul style="list-style-type: none"> <li>BV570</li> <li>Zombie Yellow</li> <li>LIVE/DEAD Yellow</li> </ul>	<ul style="list-style-type: none"> <li>BV605</li> </ul>	<ul style="list-style-type: none"> <li>BV650</li> <li>APC</li> <li>Cy5</li> <li>AF647</li> <li>LIVE/DEAD Far Red</li> </ul>	<ul style="list-style-type: none"> <li>BV711</li> <li>APC-Cy5.5</li> <li>AF700</li> </ul>	<ul style="list-style-type: none"> <li>BV785</li> <li>APC-Cy7</li> <li>APC-AF750</li> <li>APC-Fire 750</li> <li>Zombie NIR</li> <li>LIVE/DEAD NIR</li> </ul>

For 4-laser, 12-color models LE-MA900F/FP